

Product Information TFP-41, -44, -51, -54, -61, -161, -164, -181, -184

**FOOD** 

# Temperature Sensor with G1/2" hygienic



#### Application/Specified usage

- · Temperature Measurement in vessels and pipes
- Front flush temperature measurement available

#### **Application examples**

- · Monitoring of CIP-/ SIP-process
- · Measurement in vessels with agitators with front flush version
- · Temperature monitoring in milk vessels

#### Hygienic design/Process connection

- · Flow optimized, hygienic and easy sterilizable installation by using Negele weld-in sleeve, e.g. EMZ-132 or build-in system, e.g. EHG-... / 1/2"
- Additional process connections: adapters for Tri-Clamp, dairy flange (DIN 11851), Varivent, DRD, APV et al
- Sealing system free of elastomers, the connection will be without gaps and crevices
- · Product contacting materials compliant to FDA
- · Sensor completely made of stainless steel resp. PEEK (front flush sensor)
- · Conforming to 3-A Sanitary Standard 74-06 for front flush sensors

#### Features/Advantages

- · Front flush mounting possible
- · Integrated transmitter optional
- · Different electrical connections available

# **Options/Accessories**

- · 2 x Pt100 (not retrofittable)
- · 2 x Pt100 with two transmitters (not retrofittable)
- Programmable transmitters MPU-4 as well as MPU-M with output 4...20 mA, 2-wire
- · Integrated transmitters for Profibus PA and HART-protocol
- · Programming adapter MPU-P 9701
- · Integrated transmitter MPU-LCD with display in connecting head
- · Pt100 chip with other classes of accuracy (1/3B, 1/10B)
- · Fast response sensor tip 3 mm and 4 mm
- Spacer for high temperature up to 250 °C permanent temperature up to 450 °C (on request)
- · Pre-assembled connecting cable for M12-plug
- $\cdot$  Fixed cable in other lengths and other material available

#### **Authorizations**





# Temperature sensor TFP-164 / ... / MPU-M



#### Temperature sensor TFP-41



#### Accessories

PVC-cable with M12-connection made of 1.4305, IP 69 K, unshielded

M12-PVC / 4-5 mPVC-cable 4-pin, length 5 mM12-PVC / 4-10 mPVC-cable 4-pin, length 10 mM12-PVC / 4-25 mPVC-cable 4-pin, length 25 m

#### **PVC-cable with M12-connection**



2

Temperature sensor				
Process connection	thread	G1/2" combined with Negele weld-in sleeves, build-in systems, adapter sleeves		
Tightening torque	sensor sealing PEEK sensor sealing stainless steel	10 Nm 20 Nm		
Insertion length EL	TFP-41, -51, -61, -161, -181 TFP-44, -54, -164, -184	20500 mm front flush		
Materials	connecting head thermowell at TFP-44, -54, -164, -184	stainless steel 1.4305 stainless steel 1.4404 PEEK		
Operating pressure	TFP-41, -51, -61, -161, -181 TFP-44, -54, -164, -184	50 bar maximum 10 bar maximum		
Temperature ranges	ambient sensor tip TFP-xx1 sensor tip TFP-xx4	-50+80 °C -50+250 °C -50+140 °C		
Sensing resistor	acc. to DIN EN 60751	Pt100		
Electrical connection	cable gland cable connection fixed cable 2.5 m fixed cable 2.5 m (≥ 90 °C)	M16 x 1,5 M12-plug 1.4305, 4-pins LIYY 4 x 0,25 mm <sup>2</sup> PTFE 4 x 0,14 mm <sup>2</sup>		
Protection class		IP 69 K (with electrical connection M12-plug)		

Transmitter MPU-4, MPU-10, MPU-H, MPU-M				
Temperature ranges	ambient storage	-40+85 °C -55+90 °C		
Measuring ranges	MPU-4, MPU-H, MPU-M	standard: -1040 °C, 050 / 100 / 150 / 200 °C special ranges free programable standard: -200850 °C configuration occurs with Profibus		
Accuracy	input	< ±0.25 °C		
Temperature drift	zero, span	< 0.01 % / K		
Supply	MPU-M, MPU-4 MPU-10 accuracy	835 V DC 932 V DC 0.01 % / V (reference: 12 V DC)		
Output	signal accuracy burden	analog 420 mA (not for MPU-10) < $\pm 0.1$ % of measurement range < $600~\Omega$ (at U $_B$ = 24 V)		
Humidity	without condensation	098 %		

Accuracy classes of temperature sensors   Tolerances for Pt100 acc. to DIN EN 60751					
Pt100	A	1/3 B	1/10 B		
0°C/100Ω	±0.15 K / ±0.06 Ω	±0.10 K / ±0.04 Ω	±0.03 K / ±0.01 Ω		
100 °C / 138.5 Ω	±0.35 K / ±0.13 Ω	±0.27 K / ±0.10 Ω	±0.08 K / ±0.03 Ω		

Electrical Connection FOOD


#### **Electrical connection without transmitter**

#### With 1 x M12 plug

3

#### With 1 X M111 ptog

## Configuration 1st M12 plug






#### **Electrical connection with transmitter**

#### With M12 plug

#### Configuration M12 plug



1: + supply 2: - supply 4...20 mA 3: not connected 4: not connected


#### With 2 x M12 plug



# Configuration 2nd M12 plug




## With cable gland



## With cable gland


#### **Configuration strip terminal**



## Electrical connection with two transmitter (TFP-61)

## With 1 x M12-plug (sensor 1 + sensor 2)

# Configuration M12-plug



1: + supply (sensor 1)

2: - supply 4...20 mA (sensor 1) 3: - supply 4...20 mA (sensor 2)

4: + supply (sensor 2)

#### With fixed cable



# Fixed cable connection with 1 x Pt100

wh ye bn gn standard rd rd wh wh PTFE

# With 2 x M12-plug (sensor 1)

# Configuration M12-plug



1: + supply (sensor 1)

2: - supply 4...20 mA (sensor 1)

3: not connected 4: not connected

# Fixed cable connection with 2 x Pt100 (LIYY)

wh ye bn gn 1st Pt100 rd bu pk gy 2nd Pt100




# Fixed cable connection with 2 x Pt100 (PTFE)

rd rd wh 1st Pt100 vt vt ye 2nd Pt100



# With 2 x M12-plug (sensor 2)

#### Configuration M12-plug




1: + supply (sensor 2)


2: - supply 4...20 mA (sensor 2)


3: not connected

4: not connected

4









# Important advice for TFP-51, -51.2 and TFP-54




Tighten the sensor only at the lower, marked in yellow spanner flat (BE = 22 mm)!

# 








#### Sensor tip diameter and response time

All temperature sensors are available with smaller sensor tips, to ensure a shorter response time. The below-mentioned times were measured by emersing a temperature sensor from room temperature into boiling water.



#### Conditions for a measuring point according to 3-A Sanitary Standard 74-06



- · The sensors TFP-44, -54, -164, -184 conforming to the 3-A Sanitary Standard.
- · The sensors are designed for CIP-/ SIP-cleaning. Maximum 140 °C / 120 minutes.
- Only with the build-in system CLEANadapt (EMZ, EMK, EHG with tube ≥ DN25, ISO 20 and G1", Adapter AMC and AMV) allowed.
- · Using the weld in sleeve EMZ, EMK the weld must comply to the requirements of the current 3-A Sanitary Standard.
- · Mounting position, self draining and the position of the leackage hole must be in accordance to current 3-A Sanitary Standard.

#### Mechanical connection/Installation



 Use only Negele CLEANadapt system for safe operation of measuring point!

# Conventional usage



- $\cdot$  Not suitable for applications in explosive areas.
- Not suitable for applications in safety-relevant system parts (SIL).

#### Transport/Storage



- · Do not store outside
- · Store in an area that is dry and dust-free
- · Do not expose to corrosive media
- · Protect against solar radiation
- · Avoid mechanical shock and vibration
- · Storage temperature -55...+90 °C
- · Relative humidity max. 98%

# Standards and guidelines



Compliance with the applicable regulations and directives is mandatory.

# Cleaning/Maintenance



· When using a pressure washer, do not point the nozzle directly at the electrical connections.

# Note on CE



- Applicable directives:
  Electromagnetic Compatibility Directive 2014/304
- Electromagnetic Compatibility Directive 2014/30/EU
- Compliance with the applicable EU directives is identified by the CE label on the product.
- The operating company is responsible for complying with the guidelines applicable to the entire installation.

#### Reshipment



- Sensors shall be clean and free of media or heatconductive paste and must not be contaminated with dangerous media!
- Use suitable transport packaging only to avoid damage of the equipment!

# Disposal



- Electrical devices should not be disposed of with household trash. They must be recycled in accordance with national laws and regulations.
- Take the device directly to a specialized recycling company and do not use municipal collection points.

Order Code FOOD

7

#### Order code for version with 1 x Pt100 TFP-41 (connecting head Ø 55 mm) TFP-44 (connecting head Ø 55 mm, front flush) TFP-51 (connecting head Ø 55 mm, with spacer) TFP-54 (connecting head Ø 55 mm, with spacer, front flush) TFP-161 (connecting head Ø 18 mm, electrical connection M12 plug) TFP-164 (connecting head Ø 18 mm, electrical connection M12 plug, front flush) (connecting head Ø 18 mm, electrical connection 2.5 m PTFE-cable, other lengths: see accessories, TFP-181 no transmitter possible!) **TFP-184** (connecting head Ø 18 mm, electrical connection 2.5 m PTFE-cable, other lengths: see accessories, front flush, no transmitter possible!) Sensor length in mm 020...500 (in steps of 5 mm) ХХХ (special length on request) Diameter thermowell in mm (not selectable for TFP-44, -54, -164, -184) 6 8 10 12 Diameter sensor tip in mm (not selectable for TFP-44, -54, -164, -184) X (no reduction) (only for thermowell 6 mm) 3 (only for thermowell 6 mm and 8 mm) 4 6 (only for thermowell 8 mm and 10 mm) 8 (only for thermowell 12 mm) Accuracy class Pt100 Α 1/3B 1/10B **Electrical connection** (not selectable for TFP-161, -164, -181, -184) PG (cable gland M16x1.5) M12 (M12 plug, standard with MPU-LCD) **Transmitter** Х (without) only for TFP-41, -44, -51 and -54 (programmable) MPU-4 MPU-10 (Profibus PA) MPU-H (HART-protocol) MPU-LCD (with display) only for TFP-161 and -164 MPU-M (programmable) Measuring range MPU (only for types with transmitter; not at MPU-LCD) -10...40 (range -10...40 °C) 0...50 (range 0...+50 °C) 0...100 (range 0...+100 °C) 0...150 (range 0...+150 °C) 0...200 (range 0...+200 °C) хх...уу (special range) PG/ MPU-4/ TFP-41/ 100/ 6/ **X**/ **A**/ 0...100

#### Order code for version with 2 x Pt100 TFP-41.2 (connecting head Ø 55 mm, 2 x Pt100, no transmitter possible!) TFP-51.2 (connecting head Ø 55 mm, 2 x Pt100, with spacer, no transmitter possible!) TFP-61 (higher connecting head Ø 55 mm, 2 x Pt100, prepared for 2 x transmitter) TFP-61-H (like TFP-61, but with spacer) TFP-181.2 (connecting head Ø 18 mm, electrical connection 2.5 m PTFE-cable; other lengths: see at accessories) Sensor Length in mm 020...500 (in steps of 5 mm) ххх (special length) Diameter thermowell in mm 10 12 Diameter sensor tip in mm Х (no reduction) 3 (only with thermowell 6 mm) (only with thermowell 6 mm and 8 mm) 4 6 (only with thermowell 8 mm and 10 mm) 8 (only with thermowell 12 mm) **Accuracy class Pt100** 1/3B 1/10B Electrical connection (only for TFP-41.2 and TFP-51.2) PG (cable gland M16x1.5) 2PG (2 x cable gland M16x1.5) 2M12 (2 x M12-plug) Electrical connection (only for TFP-61 and TFP-61-H) M12 (M12-plug) 2M12 (2 x M12-plug) Continue if TFP-61 oder TFP-61-H is selected! No further options for TFP-41.2, -51.2, -181.2! 1. Transmitter MPU-4 (programmable) Measuring range 1. MPU -10...40 (measuring range -10...40 °C) 0...50 (measuring range 0...+50 °C) 0...100 (measuring range 0...+100 °C) 0...150 (measuring range 0...+150 °C) 0...200 (measuring range 0...+200 °C) (special range) хх...уу 2. Transmitter MPU-4 (programmable) Measuring range 2. MPU -10...40 (-10...40 °C) 0...50 (0...+50 °C) 0...100 (0...+100 °C) 0...150 (0...+150 °C) (0...+200 °C) 0...200 (special) хх...уу TFP-61/ 100/ 6/ Х/ **A**/ M12/ **MPU-4/** 0...50/ **MPU-4/** 0...50