

Product Information TSM

Temperature Sensor Mini

Application/Specified usage

- · Temperature sensor in mini housing for food applications
- Aseptic temperature process connections without product contact for inline, precise and fast measurement. Prefabricated thermowells and build-in systems avoid opening process.
- Demounting the sensor without opening the process and without electrical disconnection avoid downtime of the equipment at calibration and maintenance

Application examples

- · Monitoring of CIP-/SIP-process
- · Safe temperature measurement in hot steam and pressurized pipes
- · Measurement in vessels with agitators with front flush version
- Temperature monitoring in vessels or pipes

Hygienic design/Process connection


- · Hygienic process connection with CLEANadapt or FLEXadapt
- · All wetted materials are FDA-conform
- · Sensor completely made of stainless steel or stainless steel and PEEK
- Complete overview of process connections: see order code
- The Anderson-Negele CLEANadapt and FLEXadapt system offers a flowoptimized, hygienic and easily sterilizable installation solution for sensors.

Features/Advantages

- · High accuracy and high ambient temperature resistance
- · Customer offset and slope adjustment
- · Flex hybrid mode with digital IO-Link and analog 4...20 mA
- Process temperature range -50...+250 °C / -58...+482 °F


Options/Accessories

- · 2x RTD
- · Front flush mounting
- · Integrated transmitter
- Programmable transmitters TTM.H and TTM.I using IO-Link
- · Different RTDs (Pt100, Pt1000) and classes of accuracy (A, AA, AAA)
- · Fast response sensor tip ø 3 mm / 0.12 in
- · Spacers for high process temperature up to 250 °C / 482 °F
- Extended temperature range (-200...400 °C / -328...752 °F)
- · Pre-assembled connecting cable for M12 plug
- · Hardwired cable in customer length and other material available





FOOD





Temperature sensor TSM with Tri-Clamp



Temperature sensor TSM for FLEXadapt ESF System



Temperature sensor						
Process connection	CLEANadapt FLEXadapt ESF G3/8" Sensor G3/8" Tri-Clamp Varivent Thread Plain rod	M12, G1/2", G1/2"-P, G1/2"-SP Sensor with cap nut, sensor tip ø 3mm Sensor with cap nut, sensor tip ø 4mm 1/2", 3/4", DN10, 1", 1½", 2", 2½", 3" (DIN 32676) DN10/15 (type B), DN25 (type F), DN40/50 (type N) G1/4", G1/2" (DIN ISO 228)				
Tightening torque	CLEANadapt M12, G1/2"-P, G1/2"-SP CLEANadapt G1/2"	10 Nm 20 Nm				
Dimensions	insertion length probe diameter sensor tip diameter	02000 mm / 078.74 in 3, 4, 6, 8, 10, 12 mm / 0.12, 0.16, 0.24, 0.31, 0.39, 0.47 in 3, 4, 6 mm / 0.12, 0.16, 0.24 in, see dimensional drawings				
Materials	connecting head, spacer wetted parts CLEANadapt G1/2"-P, G1/2"-SP	stainless steel 1.4301 (AISI 304) stainless steel 1.4404 (AISI 316L) PEEK, FDA 21 CFR 177.2415				
Operating pressure	CLEANadapt CLEANadapt G1/2"-P, G1/2"-SP	50 bar maximum 10 bar maximum				
Process temperature	standard range extended range	-50+250 °C / -58482 °F -200+400 °C / -328752 °F				
Resistance Temperature accuracy classes Detector (RTD) accuracy classes		Class A: ±(0.15 + 0.002 × t) °C Class AA / 1/3 DIN B: ±(0.1 + 0.0017 × t) °C Class AAA / 1/10 DIN B: ±(0.03 + 0.005 × t) °C				
Electrical connection	plug connection hardwired cable hardwired cable	M12 plug 1.4301 (AISI 304) PVC LIYY 4 × 0.25 mm² / AWG 23 (perm. process temp. ≤ 90 °C) PTFE 4 × 0.14 mm² / AWG 26 (perm. process temp. ≤ 250 °C)				
Protection class		IP 69 K (with electrical connection M12 plug)				

Transmitter T	TM.I, TTM.H
----------------------	-------------


-						
Temperature ranges ambient storage		-40+85 °C / -40185 °F -55+90 °C / -67194 °F				
Measuring ranges		standard °C: -1040, 050 / 100 / 150 / 200 °C standard °F: 0100, 0150, 0200, 30230, 0250 °F custom ranges programable				
Accuracy input repeatability		≤ 0.1 K (at ambient ≤ 85 °C / 185 °F) ≤ 0.05 K				
Temperature drift	typical maximum	5 mK/K (at 25 °C / 77 °F) 10 mK/K (at 25 °C / 77 °F)				
Adjustments	damping offset slope	0120 s ≤ ±10 K ≤ ±25 %				
Digital output	IO-Link digital resolution master cycle time power supply	v1.1 0.01 K ≤ 51.2 ms 1830 V DC according to IO-Link				
Inalog outputsignalTTM.H only)accuracytemperature drift typicaltemperature drift maxeffect of supply voltagevariationsmaximum load resistancepower supply		420 mA, 2 wire ≤ 0.05 % of upper range limit 0.0005 %/K (at 25 °C / 77 °F) 0.003 %/K (at 25 °C / 77 °F) < 0.001 %/V (at 24 V DC) R ≤ (V DC - 12 V) : 0.024 A (at 25 °C / 77 °F), see diagram 1230 V DC				


Electrical Connection

RTD

Accuracy classes of temperature sensors Tolerances for Pt100 acc. to DIN EN 60751								
Pt100 Class A Class AA / 1/3 DIN B Class AAA / 1/10								
0 °C / 100 Ω	±0.15 K / ±0.06 Ω	±0.10 K / ±0.04 Ω	±0.03 K / ±0.01 Ω					
100 °C / 138.5 Ω	±0.35 K / ±0.13 Ω	±0.27 K / ±0.10 Ω	±0.08 K / ±0.03 Ω					

Accuracy classes of temperature sensors Tolerances for Pt1000 acc. to DIN EN 60751							
Pt1000 Class A Class AA / 1/3 DIN B Class AAA / 1							
0 °C / 1000 Ω	±0.15 K / ±0.6 Ω	±0.10 K / ±0.4 Ω	±0.03 K / ±0.1 Ω				
100 °C / 1385.1 Ω	±0.35 K / ±1.3 Ω	±0.27 K / ±1.0 Ω	±0.08 K / ±0.3 Ω				







Ø**4**


[0.16]


Ø3 [0.12]




Ød












T05 | Tri-Clamp 1/2", 1/4"





Vxx | Varivent




NO1 | Plain rod



Tri-Clamp size						
Туре	Type ø D [mm / inch]					
T10	34.0 / 1.34					
TC1	50.5 / 1.99					
TC2	64.0/2.52					
T25	77.5 / 3.05					
TC3	91.0 / 3.58					

Dimensions table Varivent					
Туре	Varivent Type	D1 [mm / inch]	D2 [mm / inch]		
V10	В	52.7 / 2.09	31.0 / 1.22		
V25	F	66.0 / 2.60	50.0 / 1.97		
V40	Ν	84.0/3.31	68.0 / 2.68		

Sensor tip diameter and response time



FOOD

Mechanical connection/Installation

· Use Negele CLEANadapt or FLEXadapt system for safe operation of measuring point!

Transport/Storage



- · Do not store outside
- · Store in an area that is dry and dust-free
- Do not expose to corrosive media
- Protect against solar radiation
- Avoid mechanical shock and vibration
- Storage temperature -55...+90 °C / -67...194 °F
- · Relative humidity max. 98 %

Cleaning/Maintenance



· When using a pressure washer, do not point the nozzle directly at the electrical connections.

Reshipment



- · Sensors shall be clean and free of media or heatconductive paste and must not be contaminated with dangerous media!
- · Use suitable transport packaging only to avoid damage of the equipment!

Conventional usage




· Not suitable for applications in explosive areas. Not suitable for applications in safety-relevant system parts (SIL).

Standards and guidelines

 Compliance with the applicable regulations and direct tives is mandatory.

Note on CE



- Electromagnetic Compatibility Directive 2014/30/EU
- · Compliance with the applicable EU directives is identified by the CE label on the product.
- · The operating company is responsible for complying with the guidelines applicable to the entire installation.

Disposal

- · Electrical devices should not be disposed of with household trash. They must be recycled in accordance with national laws and regulations.
- Take the device directly to a specialized recycling company and do not use municipal collection points.



7

Order code

TSMF Temperatur Sensor Mini for Food Applications, material wetted parts 1.4404 (AISI 316L)

Standard temperature range (-50...250 °C / -58...482 °F) Ext. temperature range (-200...400 °C / -328...752 °F) **Process connection** Process connection T05 Tri-Clamp 1/2" and 3/4" CH1 CLEANadapt M12 (incl. spacer) T10 Tri-Clamp DN10 CH₂ CLEANadapt G1/2" (incl. spacer) TC1 Tri-Clamp 1" and 11/2" GH1 Thread G1/2" (incl. spacer) Tri-Clamp 2" TC2 NH1 Plain rod (incl. spacer) T25 Tri-Clamp 21/2" TC3 Tri-Clamp 3" V10 Varivent type B DN10/15 V25 Varivent type F DN25 V40 Varivent type N DN40/50 C01 CLEANadapt M12 C02 CLEANadapt G1/2" C03 CLEANadapt G1/2"-P (PEEK) C04 CLEANadapt G1/2"-SP (short version, PEEK) N01 Plain rod Thread G1/2" G01 G02 Thread G1/4" Process connection without media contact FLEXadapt ESF G3/8" with cap nut, sensor tip ø 3 mm M02 M03 Sensor G3/8" with cap nut, sensor tip Ø 4 mm Spacer extension Х Without spacer (perm. process temp. \leq 100 °C / 212 °F, standard for extended temperatur range) S Short spacer (permanent process temperature ≤ 150 °C / 305 °F) Н Long spacer (permanent process temperature ≤ 250 °C / 482 °F) RTD type 0 1x Pt100 A, 2-wire (probe length \leq 250 mm) 1x Pt100 AA, 2-wire (probe length \leq 250 mm) 1 2 2x Pt100 A, 2-wire (probe length $\leq 250 mm$) 3 2x Pt100 AA, 2-wire (probe length \leq 150 mm) 1x Pt100 A, 4-wire (probe length \geq 50 mm) 4 5 1x Pt100 AA, 4-wire (probe length \geq 50 mm) 6 1x Pt100 AAA, 4-wire 7 2x Pt100 A, (3) 4-wire (probe length \geq 50 mm, 3-wire with sensor tip ø 3 mm) 2x Pt100 AA, (3) 4-wire (probe length \geq 50 mm, 3-wire with sensor tip ø 3 mm) 8 9 2x Pt100 AAA, 4-wire 1x Pt1000 A, 2-wire Α Probe length for process connection [mm] Variable probe length [mm] 0...50 In steps of 5 mm M02 M03 C03, C04 51...250 In steps of 5 mm 37 68 0 251...500 148 10 In steps of 10 mm 59 In steps of 50 mm 501...1000 83 198 1001...2000 In steps of 100 mm 97 234 intermediate Not for M02, M03, 160 238 C03, C04 lengths 249 **Probe diameter** 03 3 mm (standard for M02, not for xHx) 04 4 mm (standard for M03) 06 6 mm 8 mm (standard for C03, C04 with sensor tip) 08 10 mm (standard for C03, C04 frontflush, not for Txx, Vxx) 10 12 12 mm (not for Txx, Vxx) Sensor tip diameter, only for probe length ≥ 50 mm Without reduction (standard for M02, M03) Х For probe diameter 6 mm 3 For probe diameter 6, 8, 10 mm 4 6 For probe diameter 8, 10, 12 mm

Order code										
Order code						Mat 0 1	(stai 1.44	404 (AIS ndard fo 404 (AIS f ace fini	or CO3, C 5l 316L) i sh 8 µm / 3 nitter Withou TTM.I (TTM.H	without certificate 04, G01, G02, M02, M03) ncl. material certificate 2 µin It transmitter IO-Link only) (hybrid: analog and IO-Link) rement range Without transmitter Unit °C (only for TTM.I) Unit °F (only for TTM.I) Unit °F (only for TTM.I) Unit K (only for TTM.I) Unit K (only for TTM.I) Unit K (only for TTM.I) -1040 °C 050 °C 0150 °C 0200 °C 0250 °C 0200 °F 30230 °F 0230 °F 0250 °F TTM custom configuration Electrical connection with transmitter 4 M12 plug (4 pin) Electrical connection without transmitter 4 M12 plug (4 pin) 1x RTD 8 M12 plug (8 pin) 2x RTD P PVC-cable ($\leq 90 °C / 194 °F$) T PTFE-cable ($\leq 250 °C / 482 °F$) Cable length [m] (with hardwired cable only) 150
TSMF/ CO)1/ X	/ 0/	∀ 100 /	∀ 06 /	4/	¥ 0/	₩ 0/	∀ 0/	∀ 000 /	Ψ Ψ P/ 12

Accessories

PVC-cable with M12 connection made of 1.4305 (AISI 303), IP 69 K, unshielded

M12-PVC / 4-5 m M12-PVC / 4-10 m M12-PVC / 4-25 m PVC-cable 4 pin, length 5 m PVC-cable 4 pin, length 10 m PVC-cable 4 pin, length 25 m

TPE-cable with M12 connection made of 1.4571 (AISI 316Ti), IP 69, shielded

M12-TPE / 8-5 m M12-TPE / 8-10 m TPE-cable 8 pin, length 5 m TPE-cable 8 pin, length 10 m

PVC-cable with M12-connection



FOOD

Order code

50118 / 1.0 / 2020-10-28 / AR / EN

ANDERSON INSTRUMENT COMPANY 156 Auriesville Road Fultonville, NY 12072, USA Phone 800-833-0081 info@anderson-negele.com techservice@anderson-negele.com NEGELE MESSTECHNIK GMBH Raiffeisenweg 7 87743 Egg an der Guenz, GERMANY Phone +49 (0) 83 33 . 92 04 - 0 sales@anderson-negele.com support@anderson-negele.com